



UK Sampling Gauges Ltd

Building 1, Roman Bank, Bourne, Lincolnshire, PE10 9LQ, UK

Tel: +44 (0)1778 392818 Fax: +44 (0)1778 421169

E-mail: sales@samplinggauges.com

Web site: www.samplinggauges.com



All-level Sampler RNS 1002

Application

This All-level Sampler has been developed to take an accurate sample of liquid from the total contents of a tank. It collects its sample from the tank continuously as it moves downwards through the liquid from top to bottom. The sampler has a special valve to allow liquid to enter only while the sampler is moving downwards. The valve closes if the descent of the sampler is interrupted for any reason, and it remains closed while the sampler is withdrawn from the tank.

The sampler also has a new (patent applied for) design feature to ensure that the rate of filling is constant during operation, independent of both the depth of the sampler and the extent of filling. The top of the tube acts as a level indicator to check that the sampler is 70% - 80% full after sampling. These features together simplify the operator's task in taking an accurate sample.

The sampler has been developed to enable the samples to be decanted through the top cap, without the need for dismantling or unscrewing any sealing caps.

The sampler can be dismantled by hand for cleaning, as the photograph shows.

Different inlet probe sizes are available, so that the sampler can be used to sample a wide range of liquid densities and viscosities, and tank depths, within practical time limits. These probes can be interchanged easily by the operator on-site.



RNS 1002

Specifications

| | RNS 1002 |
|------------------|---------------------|
| Overall diameter | 64mm |
| Overall length | 59cm |
| Capacity | 1000ml |
| Material | 316 Stainless Steel |

Operation

The RNS 1002 sampler is designed for use in closed sampling, with our MK 10 Winder. The (similar) RNS 1002 S sampler can be used in open sampling, together with our MK 1B Winder.

Please contact us if you require further information about these or other equipment offered by **UK Sampling Gauges Ltd**, or if you require equipment to be adapted or modified.